

DRUM MASSAGER- DM2

2715 North Airport Commerce Ave. Springfield, MO 65803 Phone: (417) 868-8002 Fax: (417) 868-8316 www.custom-powder.com




Apprciate the Art of Engineering

What's the safest and easiest way to break up hardened product in your drums or boxes? Enter the CPS Drum Massager. No matter the material, our massager can handle it. Discharging has never been easier!

From food to chemical to pharmaceutical, Custom Powder Systems and Integrated Containment Systems serve a multitude of industries as a leading provider in Dry Material Handling/Process Equipment. We design, manufacture, integrate, and test all of our systems in-house and our highly experienced technical services team will respond quickly to any need that arises. Whatever the powder handling question, we've got the answer.

custom-powder.com

DRUM MASSAGER- DM2



- •304 Stainless Steel
- 35 Ra u-inch Bright Polish VisibleMaterial Finishes
- Easy-clean Pharmaceutical cGMP Design
- Handles 24-to-12-inch Diameter Fiber Drums and Plastic Drums Up to 38-inches Tall
- See-through Door With Sidewall Windows
- Washdown Design with NEMA 4X Electrical Enclosure Rating
- 6-inch Color Touchscreen Control Interface
- 115 VAC Single Phase 60 Hz 20 Amp Power
- Allen Bradley MicroLogix PLC
- Rolling Shade Barrier Covering Machinery
- Jaw Pressure Control

UPGRADED FEATURES

- Casters
- Stacklight Status Indicator
- Left-Hand Side Control Interface
- Vacuum Tube Lift Loader
- Explosion-Proof Class 1, Division 1/2
- Explosion-Proof Class 2, Division 1
- Box Massaging Adapter
- Small Drum Adapter
- Conveyor Loading System



BASE MODEL